

FGA 33 NBR-ESD-55 N018


Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR-ESD
Malzeme sertliği [Shore A]	55,0 Shore A
Boyut	33,00
Körük Sayısı	1,5

Tasarım verileri

Attribute	Value
Yükseklik H2	13,00 mm
Yükseklik H	27,00 mm
Dış çap D1	36,0 mm
Kafa çapı Dk	18,0 mm
İç çap d1	16,0 mm
d2	17,0 mm
İç çap d	8,00 mm
Yay stroku Z	9,0 mm
Çap Ds	30,0 mm
Yükseklik H3	14,00 mm
Çap Dmax(S)	38,0 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları



Tasarım verileri FGA 33 NBR-ESD-55 N018

Art.-Nr.: 10.01.06.04456

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR-ESD
İş parçası yarıçapı dak (dışbükey)	40,0 mm
Emme kuvveti (-600mbar)	13,60 N
Ağırlık	7,30 g
Boyut	33,00
Körük Sayısı	1,5
Ürün ailesi	FGA

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.04456

**Sipariş Verisi Aksesuarlar 10.01.06.04456**

Typ	Ürün numarası
Vantuz bağlantı nipeli	SA-NIP N018 G1/4-AG DN440
Vantuz bağlantı nipeli	SA-NIP N018 G1/4-IG DN440

WWW.SCHMALZ.COM/10.01.06.04456