

Art.-Nr.: 10.01.06.04530



SPB1 30 ED-65 G1/4-AG

Technical data


Attribute	Value
Suction cup material	Elastodur ED
Material hardness [Shore A]	65.0 Shore A
Size	30.00
Number of folds	1.5
Thread G1	G1/4"-M

Suction cup SPB1 (elastomer part + connection element) is delivered assembled. The assembly consists of:

- Suction cup of type SPB1 – elastomer part, available in various diameters
- Connection element of type SC – available with various threads

Available spare parts: suction cup SPB1, connection element (Schmalz-Connector)

Available accessories: filter screen (sieve, round), suction cup insert



Design data SPB1 30 ED-65 G1/4-AG

Design data

Attribute	Value
Height H	29.00 mm
Nominal diameter dn	4.10 mm
d2	20.0 mm
Thread G1	G1/4"-M
Thread length LG1	10.0 mm
Key width SW1	17.0 mm
Spring stroke Z	13.0 mm
Diameter Ds	31.4 mm
Diameter Dmax(S)	36.7 mm



Bellows suction cups (round)

SPB1 30 ED-65 G1/4-AG



Art.-Nr.: 10.01.06.04530



Technical data

Attribute	Value
Suction cup material	Elastodur ED
Material hardness [Shore A]	65.0 Shore A
Hose inner diameter (recom.) d	6.0 mm
Workpiece radius min. (convex)	25.0 mm
Pull-off force	30.60 N
Suction force (-600mbar)	20.70 N
Lateral force	15.5 N
Volume	7.993 cm ³
Size	30.00
Number of folds	1.5
Product family	SPB1

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.04530



Ordering Data Accessories 10.01.06.04530

Typ	Item number
Sieve, round	SIEB 11x1 MS-A2 280 0.28/0.16
	10.07.01.00309



Ordering Data Spare Parts 10.01.06.04530

Typ	Item number
Bellows suction cup (round)	SPB1 30 ED-65 SC040
Schmalz-Connector	SC 040 G1/4-AG
	10.01.06.02454
	10.01.06.03414



WWW.SCHMALZ.COM/10.01.06.04530