


Bellows suction cup f SCG(S)-gripper

# BCG 20 SI-MD-55 SC085




Art.-Nr.: 10.01.06.04558



BCG 20 SI-MD-55 SC085

### Technical data

| Attribute                   | Value                        |
|-----------------------------|------------------------------|
| Suction cup material        | Silicone SI metal detectable |
| Material hardness [Shore A] | 55.0 Shore A                 |
| Size                        | 20.00                        |



Design data BCG 20 SI-MD-55 SC085

### Design data

| Attribute        | Value    |
|------------------|----------|
| Height H         | 13.00 mm |
| d2               | 15.5 mm  |
| Spring stroke Z  | 3.0 mm   |
| Diameter Ds      | 21.5 mm  |
| Diameter Dmax(S) | 25.0 mm  |



### Technical data

| Attribute                   | Value                        |
|-----------------------------|------------------------------|
| Suction cup material        | Silicone SI metal detectable |
| Material hardness [Shore A] | 55.0 Shore A                 |
| Weight                      | 2.0 g                        |



[WWW.SCHMALZ.COM/10.01.06.04558](http://WWW.SCHMALZ.COM/10.01.06.04558)

Bellows suction cup f SCG(S)-gripper

## BCG 20 SI-MD-55 SC085



Art.-Nr.: 10.01.06.04558



### Further documentation

CAD data and other documents relating to the article can be found at: [www.schmalz.com/10.01.06.04558](http://www.schmalz.com/10.01.06.04558)



[WWW.SCHMALZ.COM/10.01.06.04558](http://WWW.SCHMALZ.COM/10.01.06.04558)