




SFB1 10 NBR-ESD-55 SC030

Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR-ESD
Malzeme sertliği [Shore A]	55,0 Shore A
Boyut	10,00
Körük Sayısı	1,5

Tasarım verileri

Attribute	Value
Yükseklik H2	4,20 mm
Yükseklik H	12,30 mm
Dış çap D1	8,2 mm
Kafa çapı Dk	8,7 mm
İç çap d1	7,3 mm
d2	3,4 mm
İç çap d	5,50 mm
Yay stroku Z	2,5 mm
Çap Ds	10,0 mm
Çap Dmax(S)	11,0 mm



Tasarım verileri SFB1 10 NBR-ESD-55 SC030

Art.-Nr.: 10.01.06.04595

**Teknik veriler**

Attribute	Value
Meme ucu ailesi	SC 030
Vantuz malzemesi	Nitril kauçuk NBR-ESD
Malzeme sertliği [Shore A]	55,0 Shore A
İş parçası yarıçapı dak (dışbükey)	10,0 mm
Çekme kuvveti	2,70 N
Emme kuvveti (-600mbar)	0,50 N
Cilt	0,287 cm ³
Boyut	10,00
Körük Sayısı	1,5
Ürün ailesi	SFB1

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.04595

**Sipariş Verisi Aksesuarlar 10.01.06.04595**

Typ	Ürün numarası
Schmalz-Konnektör	SC 030 M5-AG
	10.01.06.02802

WWW.SCHMALZ.COM/10.01.06.04595