


Art.-Nr.: 10.01.06.04786



SFB1 40 NBR-ESD-55 SC050



Design data SFB1 40 NBR-ESD-55 SC050

Technical data

Attribute	Value
Suction cup material	Nitrile rubber NBR-ESD
Material hardness [Shore A]	55.0 Shore A
Size	40.00
Number of folds	1.5

Design data

Attribute	Value
Height H2	6.60 mm
Height H	29.70 mm
Outside diameter D1	29.8 mm
Head diameter Dk	20.0 mm
Internal diameter d1	17.0 mm
d2	13.7 mm
Internal diameter d	11.40 mm
Spring stroke Z	10.0 mm
Diameter Ds	40.0 mm
Diameter Dmax(S)	42.0 mm

Art.-Nr.: 10.01.06.04786

**Technical data**

Attribute	Value
Nipple family	SC 050
Suction cup material	Nitrile rubber NBR-ESD
Material hardness [Shore A]	55.0 Shore A
Workpiece radius min. (convex)	30.0 mm
Pull-off force	39.90 N
Suction force (-600mbar)	8.80 N
Weight	7.5 g
Volume	7.533 cm ³
Size	40.00
Number of folds	1.5
Product family	SFB1

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.04786

**Ordering Data Accessories 10.01.06.04786**

Typ		Item number
Schmalz-Connector	SC 050 G1/4-AG SW410	10.01.06.04347
Schmalz-Connector	SC 050 G1/4-IG SW410	10.01.06.04348

