



SFB1 10 NBR-ESD-55 M5-AG

Vantuz SFB1 (elastomer parça + bağlantı nipeli) monte edilmiş olarak teslim edilir.


Mevcut yedek parçalar: vantuz SFB1, bağlantı nipeli SC

Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR-ESD
Malzeme sertliği [Shore A]	55,0 Shore A
Boyut	10,00

Tasarım verileri

Attribute	Value
Yükseklik H	17,30 mm
Nominal çap dn	1,80 mm
Dış uzunluğu LG1	4,7 mm
Anahtar boyutu SW1	8,0 mm
Yay stroku Z	2,5 mm
Çap Ds	10,0 mm
Çap Dmax(S)	11,0 mm
Dış G1	M5-AG



Tasarım verileri SFB1 10 NBR-ESD-55 M5-AG

Art.-Nr.: 10.01.06.04788

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR-ESD
Malzeme sertliği [Shore A]	55,0 Shore A
Çekme kuvveti	2,70 N
Emme kuvveti (-600mbar)	0,50 N
Ağırlık	1,60 g
Cilt	0,300 cm ³
Boyut	10,00
Körük Sayısı	1,5
Ürün ailesi	SFB1

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.04788

**Sipariş Verisi Yedek Parça 10.01.06.04788**

Typ	Ürün numarası
Körüklü vantuz (yuvarlak)	SFB1 10 NBR-ESD-55 SC030
Schmalz-Konnektör	SC 030 M5-AG

