


Art.-Nr.: 10.01.06.04793



SFB1 20 NBR-ESD-55 G1/8-IG

Vantuz SFF / SFB1 (elastomer parça + bağlantı nipeli) monte edilmiş olarak teslim edilir.

Mevcut yedek parçalar: vantuz SFF / SFB1, bağlantı nipeli SC



Tasarım verileri SFB1 20 NBR-ESD-55 G1/8-IG

Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR-ESD
Malzeme sertliği [Shore A]	55.0 Shore A
Boyut	20.00

Tasarım verileri

Attribute	Value
Yükseklik H	31.50 mm
Nominal çap dn	4.10 mm
Diş uzunluğu LG1	8.0 mm
Anahtar boyutu SW1	14.0 mm
Yay stroku Z	5.0 mm
Çap Ds	20.0 mm
Çap Dmax(S)	21.0 mm
Diş G1	G1/8-IG



Art.-Nr.: 10.01.06.04793

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR-ESD
Malzeme sertliği [Shore A]	55.0 Shore A
Çekme kuvveti	10.50 N
Emme kuvveti (-600mbar)	2.10 N
Ağırlık	6.6 g
Cilt	1.200 cm ³
Boyut	20.00
Körük Sayısı	1.5
Ürün ailesi	SFB1

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.04793

**Yedek parçalar için sipariş verileri 10.01.06.04793**

Typ	Ürün numarası
Körüklü vantuz (yuvarlak)	SFB1 20 NBR-ESD-55 SC040 10.01.06.04784
Schmalz-Konnektör	SC 040 G1/8-IG 10.01.06.02482

