

Art.-Nr.: 10.01.06.04796




Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR-ESD
Malzeme sertliği [Shore A]	55.0 Shore A
Boyut	30.00

SFB1 30 NBR-ESD-55 G1/4-AG

Vantuz SFF / SFB1 (elastomer parça + bağlantı nipeli) monte edilmiş olarak teslim edilir.

Mevcut yedek parçalar: vantuz SFF / SFB1, bağlantı nipeli SC



Tasarım verileri

Attribute	Value
Yükseklik H	26.40 mm
Nominal çap dn	4.10 mm
Diş uzunluğu LG1	10.0 mm
Anahtar boyutu SW1	17.0 mm
Yay stroku Z	8.0 mm
Çap Ds	30.0 mm
Çap Dmax(S)	31.5 mm
Diş G1	G1/4-AG

Tasarım verileri SFB1 30 NBR-ESD-55 G1/4-AG



Art.-Nr.: 10.01.06.04796

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR-ESD
Malzeme sertliği [Shore A]	55.0 Shore A
Çekme kuvveti	23.70 N
Emme kuvveti (-600mbar)	4.60 N
Ağırlık	10.1 g
Cilt	2.900 cm ³
Boyut	30.00
Körük Sayısı	1.5
Ürün ailesi	SFB1

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.04796

**Yedek parçalar için sipariş verileri 10.01.06.04796**

Typ	Ürün numarası
Körüklü vantuz (yuvarlak)	SFB1 30 NBR-ESD-55 SC040
Schmalz-Konnektör	SC 040 G1/4-AG

WWW.SCHMALZ.COM/10.01.06.04796