




Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR-ESD
Malzeme sertliği [Shore A]	55.0 Shore A
Boyut	40.00

SFB1 40 NBR-ESD-55 G1/4-IG

Vantuz SFF / SFB1 (elastomer parça + bağlantı nipeli) monte edilmiş olarak teslim edilir.

Mevcut yedek parçalar: vantuz SFF / SFB1, bağlantı nipeli SC



Tasarım verileri

Attribute	Value
Yükseklik H	46.90 mm
Nominal çap dn	4.10 mm
Diş uzunluğu LG1	12.0 mm
Anahtar boyutu SW1	17.0 mm
Yay stroku Z	10.0 mm
Çap Ds	40.0 mm
Çap Dmax(S)	42.0 mm
Diş G1	G1/4-IG

Tasarım verileri SFB1 40 NBR-ESD-55 G1/4-IG



Art.-Nr.: 10.01.06.04799

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR-ESD
Malzeme sertliği [Shore A]	55.0 Shore A
Çekme kuvveti	39.90 N
Emme kuvveti (-600mbar)	8.80 N
Ağırlık	18.2 g
Cilt	7.500 cm ³
Boyut	40.00
Körük Sayısı	1.5
Ürün ailesi	SFB1

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.04799

**Yedek parçalar için sipariş verileri 10.01.06.04799**

Typ	Ürün numarası
Körüklü vantuz (yuvarlak)	SFB1 40 NBR-ESD-55 SC050
Schmalz-Konnektör	SC 050 G1/4-IG SW410

WWW.SCHMALZ.COM/10.01.06.04799