

Körüklü vantuz (yuvarlak)

FGC 40 NBR-55 SC080




Art.-Nr.: 10.01.06.04863



FGC 40 NBR-55 SC080

Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	55.0 Shore A
Boyut	40.00
Körük Sayısı	4.5
Arayüz meme ucu ailesi	SC080



Tasarım verileri FGC 40 NBR-55 SC080

Tasarım verileri

Attribute	Value
Yükseklik H2	13.00 mm
Yükseklik H	47.00 mm
Dış çap D1	39.0 mm
Kafa çapı Dk	25.0 mm
d2	27.5 mm
İç çap d	16.00 mm
Yay stroku Z	25.0 mm
Çap Ds	39.0 mm
Çap Dmax(S)	41.0 mm



WWW.SCHMALZ.COM/10.01.06.04863

Art.-Nr.: 10.01.06.04863



Teknik veriler

Attribute	Value
Meme ucu ailesi	SC 080
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	55.0 Shore A
Emme kuvveti (-600mbar)	35.00 N
Boyut	40.00
Körük Sayısı	4.5
Ürün ailesi	FGC

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.04863

