




SPB1 25 ED-65 NPT1/8-IG

Suction cup SPB1 (elastomer part + connection element) is delivered assembled. The assembly consists of:

- Suction cup of type SPB1 – elastomer part, available in various diameters
- Connection element of type SC – available with various threads

Available spare parts: suction cup SPB1, connection element (Schmalz-Connector)

Available accessories: filter screen (sieve, round), suction cup insert



Design data SPB1 25 ED-65 NPT1/8-IG

Technical data

Attribute	Value
Suction cup material	Elastodur ED
Material hardness [Shore A]	65.0 Shore A
Size	25.00
Number of folds	1.5
Thread G1	NPT1/8"-F

Design data

Attribute	Value
Height H	35.00 mm
Nominal diameter dn	4.10 mm
d2	16.9 mm
Thread G1	NPT1/8"-F
Thread length LG1	10.5 mm
Key width SW1	14.0 mm
Spring stroke Z	11.0 mm
Diameter Ds	26.4 mm
Diameter Dmax(S)	31.3 mm

Art.-Nr.: 10.01.06.04951

**Technical data**

Attribute	Value
Suction cup material	Elastodur ED
Material hardness [Shore A]	65.0 Shore A
Hose inner diameter (recom.) d	4.0 mm
Workpiece radius min. (convex)	20.0 mm
Pull-off force	23.40 N
Suction force (-600mbar)	14.90 N
Weight	8.10 g
Lateral force	13.0 N
Volume	5.254 cm ³
Size	25.00
Number of folds	1.5
Product family	SPB1

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.04951

**Ordering Data Spare Parts 10.01.06.04951**

Typ		Item number
Schmalz-Connector	SC 040 NPT1/8-IG	10.01.06.02542
Bellows suction cup (round)	SPB1 25 ED-65 SC040	10.01.06.02453

