

Art.-Nr.: 10.01.06.04988




SPB4 20 SI-HD NPT1/4-AG

Suction cup SPB4 (elastomer part + connection element) is delivered assembled. The assembly consists of:

- Suction cup of type SPB4 – elastomer part, available in various diameters
- Connection element of type SC – available with various threads

Available spare parts: suction cup SPB4, connection element (Schmalz-Connector)

Available accessories: filter screen (sieve, round), hose clamp, pad insert



Design data SPB4 20 SI-HD NPT1/4-AG

Technical data

Attribute	Value
Suction cup material	Silicone SI-HD
Size	20.00
Number of folds	4.5
Thread G1	NPT1/4"-M

Design data

Attribute	Value
Height H	48.40 mm
Nominal diameter dn	8.00 mm
d2	13.5 mm
Thread G1	NPT1/4"-M
Thread length LG1	10.2 mm
Key width SW1	22.0 mm
Spring stroke Z	10.0 mm
Diameter Ds	21.4 mm
Diameter Dmax(S)	24.4 mm

Art.-Nr.: 10.01.06.04988

**Technical data**

Attribute	Value
Suction cup material	Silicone SI-HD
Hose inner diameter (recom.) d	9.0 mm
Pull-off force	11.00 N
Suction force (-600mbar)	8.00 N
Weight	20.7 g
Volume	7.900 cm ³
Size	20.00
Number of folds	4.5
Product family	SPB4

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.04988

**Ordering Data Spare Parts 10.01.06.04988**

Typ		Item number
Schmalz-Connector	SC 080 NPT1/4-AG	10.01.06.03662
Bellows suction cup SI-HD (round)	SPB4 20 SI-HD-65 SC080	10.01.06.03378

