



Technical data

Attribute	Value
Suction cup material	Silicone SI
Material hardness [Shore A]	55.0 Shore A
Size	20.00
Material characteristics	FDA-compatible

SFB1 20 SI-55 NPT1/8-IG

The suction cup SFB1 (elastomer part + connection nipple) is delivered assembled.

Available spare parts: suction cup SFB1, connection nipple SC



Design data

Attribute	Value
Height H	31.50 mm
Nominal diameter dn	4.10 mm
d2	6.6 mm
Thread length LG1	10.5 mm
Key width SW1	14.0 mm
Spring stroke Z	5.0 mm
Diameter Ds	20.0 mm
Diameter Dmax(S)	21.0 mm
Thread G1	NPT1/8-IG

Design data SFB1 20 SI-55 NPT1/8-IG

Bellows suction cups (round)

SFB1 20 SI-55 NPT1/8-IG



Art.-Nr.: 10.01.06.05112



Technical data

Attribute	Value
Suction cup material	Silicone SI
Material hardness [Shore A]	55.0 Shore A
Pull-off force	10.50 N
Suction force (-600mbar)	2.10 N
Weight	6.60 g
Volume	1.200 cm ³
Size	20.00
Number of folds	1.5
Product family	SFB1

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.05112



Ordering Data Spare Parts 10.01.06.05112

Typ		Item number
Schmalz-Connector	SC 040 NPT1/8-IG	10.01.06.02542
Bellows suction cup (round)	SFB1 20 SI-55 SC040	10.01.06.04369



WWW.SCHMALZ.COM/10.01.06.05112