



SFB1 40 HT1-60 NPT1/4-AG

The suction cup SFB1 (elastomer part + connection nipple) is delivered assembled.


Available spare parts: suction cup SFB1, connection nipple SC

Technical data

Attribute	Value
Suction cup material	High temperature material HT1
Material hardness [Shore A]	60.0 Shore A
Size	40.00

Design data

Attribute	Value
Height H	35.70 mm
Nominal diameter dn	4.10 mm
d2	13.7 mm
Thread length LG1	10.0 mm
Key width SW1	17.0 mm
Spring stroke Z	10.0 mm
Diameter Ds	40.0 mm
Diameter Dmax(S)	42.0 mm
Thread G1	NPT1/4-AG



Design data SFB1 40 HT1-60 NPT1/4-AG

Art.-Nr.: 10.01.06.05151

**Technical data**

Attribute	Value
Suction cup material	High temperature material HT1
Material hardness [Shore A]	60.0 Shore A
Pull-off force	39.90 N
Suction force (-600mbar)	8.80 N
Volume	7.500 cm ³
Size	40.00
Number of folds	1.5
Product family	SFB1

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.05151

**Ordering Data Spare Parts 10.01.06.05151**

Typ		Item number
Schmalz-Connector	SC 050 NPT1/4-AG MOD	10.01.06.04896
Bellows suction cup (round)	SFB1 40 HT1-60 SC050	10.01.06.04384

