

Körüklü vantuz (yuvarlak)

SPB2 40 SI-55 P SO



Art.-Nr.: 10.01.06.05171



Teknik veriler

Attribute	Value
Vantuz malzemesi	Silikon SI
Malzeme sertliği [Shore A]	55,0 Shore A
Boyut	40,00
Körük Sayısı	2,5
Şekil	Push In

SPB2 40 SI-55 P SO

Körüklü vantuz SPB2 P bağlanmaya hazır bir bileşen olarak teslim edilir. Tek bileşenli veya entegre akış kısıtlayıcı olarak farklı çaplarda mevcuttur.

Mevcut yedek parçalar: akış kısıtlayıcı

Mevcut aksesuarlar: filtre süzgeci

Tasarım verileri

Attribute	Value
Yükseklik H2	2,20 mm
Yükseklik H	47,00 mm
Dış çap D1	43,5 mm
Nominal çap dn	7,80 mm
İç çap d1	15,7 mm
d2	17,8 mm
İç çap d	12,50 mm
Yay stroku Z	20,0 mm
Çap Ds	42,7 mm
Yükseklik H3	7,20 mm

Tasarım verileri SPB2 40 SI-55 P SO



WWW.SCHMALZ.COM/10.01.06.05171

Körüklü vantuz (yuvarlak)

SPB2 40 SI-55 P SO



Art.-Nr.: 10.01.06.05171



Teknik veriler

Attribute	Value
Vantuz malzemesi	Silikon SI
Malzeme sertliği [Shore A]	55,0 Shore A
İş parçası yarıçapı dak (dışbükey)	75,0 mm
Çekme kuvveti	40,00 N
Emme kuvveti (-600mbar)	14,90 N
Ağırlık	18,20 g
Cilt	22,000 cm ³
Boyut	40,00
Körük Sayısı	2,5
Ürün ailesi	SPB2

Note: Suction force: The suction force values are theoretical values at -600 mbar vacuum and a dry, smooth and even workpiece surface - they are given without safety factors



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.05171



WWW.SCHMALZ.COM/10.01.06.05171