


Körüklü vantuz (yuvarlak)

FSDC 40 SI-MD-55 N059



Art.-Nr.: 10.01.06.05187




FSDC 40 SI-MD-55 N059

Teknik veriler

Attribute	Value
Vantuz malzemesi	Silikon SI metal algılanabilir
Malzeme sertliği [Shore A]	55.0 Shore A
Boyut	40.00
Körük Sayısı	4.5
Arayüz meme ucu ailesi	N059

Tasarım verileri

Attribute	Value
Yükseklik H2	2.40 mm
Yükseklik H	38.00 mm
Dış çap D1	41.5 mm
d2	26.9 mm
İç çap d	14.50 mm
Yay stroku Z	27.0 mm
Çap Ds	42.0 mm
Çap Dmax(S)	45.0 mm



Tasarım verileri FSDC 40 SI-MD-55 N059



WWW.SCHMALZ.COM/10.01.06.05187

Art.-Nr.: 10.01.06.05187

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Silikon SI metal algılanabilir
Çekme kuvveti	39.00 N
Emme kuvveti (-600mbar)	35.90 N
Cilt	30.600 cm ³
Boyut	40.00
Körük Sayısı	4.5
Ürün ailesi	FSDC
Arayüz meme ucu ailesi	N059

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.05187

**Veri aksesuarları sipariş edin 10.01.06.05187**

Typ		Ürün numarası
Vantuz bağlantı nipel	SA-NIP N059 G3/8-AG	10.01.06.05231
Vantuz bağlantı nipel	SA-NIP N059 G1/4-IG	10.01.06.04227

WWW.SCHMALZ.COM/10.01.06.05187