

Körüklü vantuz (yuvarlak)

FGC 60 NBR-55 SC090




Art.-Nr.: 10.01.06.05241



FGC 60 NBR-55 SC090

Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	55.0 Shore A
Boyut	60.00
Körük Sayısı	4.5
Arayüz meme ucu ailesi	SC090



Tasarım verileri FGC 60 NBR-55 SC090

Tasarım verileri

Attribute	Value
Yükseklik H2	14.00 mm
Yükseklik H	60.50 mm
Dış çap D1	60.0 mm
Kafa çapı Dk	34.0 mm
d2	41.5 mm
İç çap d	20.00 mm
Yay stroku Z	32.0 mm
Çap Ds	58.0 mm
Çap Dmax(S)	61.0 mm



WWW.SCHMALZ.COM/10.01.06.05241

Art.-Nr.: 10.01.06.05241



Teknik veriler

Attribute	Value
Meme ucu ailesi	SC 090
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	55.0 Shore A
Emme kuvveti (-600mbar)	80.00 N
Boyut	60.00
Körük Sayısı	4.5
Ürün ailesi	FGC

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.05241

