

Körüklü vantuz (yuvarlak)

PSPF 43 SI-30/55 SC080




Art.-Nr.: 10.01.06.05244



PSPF 43 SI-30/55 SC080

Teknik veriler

Attribute	Value
Vantuz malzemesi	Silikon SI
Malzeme sertliği [Shore A]	30.0 Shore A
Boyut	43.00
Körük Sayısı	3.5
Malzeme sertliği	55.0 Shore A
Malzeme özellikleri	FDA uyumlu



Tasarım verileri PSPF 43 SI-30/55 SC080

Tasarım verileri

Attribute	Value
Yükseklik H2	13.00 mm
Yükseklik H	46.60 mm
Kafa çapı Dk	21.0 mm
İç çap d1	19.6 mm
d2	18.2 mm
İç çap d	16.00 mm
Yay stroku Z	19.3 mm
Çap Ds	43.0 mm
Yükseklik H3	14.40 mm
Çap Dmax(S)	43.5 mm



WWW.SCHMALZ.COM/10.01.06.05244

Körüklü vantuz (yuvarlak)

PSPF 43 SI-30/55 SC080



Art.-Nr.: 10.01.06.05244



Teknik veriler

Attribute	Value
Vantuz malzemesi	Silikon SI
Malzeme sertliği [Shore A]	30.0 Shore A
Emme kuvveti (-600mbar)	40.00 N
Cilt	16.651 cm ³
Boyut	43.00
Körük Sayısı	3.5
Malzeme sertliği	55.0 Shore A
Ürün ailesi	PSPF
Malzeme özellikleri	FDA uyumlu

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.05244



WWW.SCHMALZ.COM/10.01.06.05244