

Körüklü vantuz (yuvarlak)

PSPF 53 SI-30/55 SC090


Art.-Nr.: 10.01.06.05505



PSPF 53 SI-30/55 SC090

Teknik veriler

Attribute	Value
Vantuz malzemesi	Silikon SI
Malzeme sertliği [Shore A]	30,0 Shore A
Boyut	53,00
Körük Sayısı	3,5
Malzeme sertliği	55,0 Shore A
Malzeme özellikleri	FDA uyumlu



Tasarım verileri PSPF 53 SI-30/55 SC090

Tasarım verileri

Attribute	Value
Yükseklik H2	14,00 mm
Yükseklik H	56,00 mm
Kafa çapı Dk	27,0 mm
İç çap d1	24,8 mm
d2	22,4 mm
İç çap d	20,00 mm
Yay stroku Z	25,3 mm
Çap Ds	53,0 mm
Yükseklik H3	16,00 mm
Çap Dmax(S)	54,5 mm



WWW.SCHMALZ.COM/10.01.06.05505

Körüklü vantuz (yuvarlak)

PSPF 53 SI-30/55 SC090



Art.-Nr.: 10.01.06.05505



Teknik veriler

Attribute	Value
Vantuz malzemesi	Silikon SI
Malzeme sertliği [Shore A]	30,0 Shore A
Emme kuvveti (-600mbar)	61,00 N
Cilt	31,854 cm ³
Boyut	53,00
Körük Sayısı	3,5
Malzeme sertliği	55,0 Shore A
Ürün ailesi	PSPF
Malzeme özellikleri	FDA uyumlu

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.05505



WWW.SCHMALZ.COM/10.01.06.05505