

Körüklü vantuz 2C (yuvarlak)

SDC1 60 PU 30/60 N044

Art.-Nr.: 10.01.06.05522




SDC1 60 PU 30/60 N044

Teknik veriler

Attribute	Value
Vantuz malzemesi	Poliüretan PU
Malzeme sertliği [Shore A]	30.0 Shore A
Boyut	60.00
Körük Sayısı	1.5
Malzeme sertliği	60.0 Shore A

Tasarım verileri

Attribute	Value
Yükseklik H2	8.00 mm
Yükseklik H	33.10 mm
Dış çap D1	60.0 mm
Kafa çapı Dk	32.0 mm
İç çap d1	14.0 mm
d2	35.2 mm
İç çap d	10.50 mm
Yay stroku Z	16.0 mm
Çap Ds	57.2 mm
Yükseklik H3	17.10 mm



Tasarım verileri SDC1 60 PU 30/60 N044



WWW.SCHMALZ.COM/10.01.06.05522

Art.-Nr.: 10.01.06.05522



Teknik veriler

Attribute	Value
Vantuz malzemesi	Poliüretan PU
Malzeme sertliği [Shore A]	30.0 Shore A
İş parçası yarıçapı dak (dışbükey)	25.0 mm
Çekme kuvveti	110.30 N
Emme kuvveti (-600mbar)	58.40 N
Cilt	30.000 cm ³
Boyut	60.00
Sıcaklık direnci	55.0 °C
Körük Sayısı	1.5
Malzeme sertliği	60.0 Shore A

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.05522

