




Teknik veriler

Attribute	Value
Vantuz malzemesi	Poliüretan PU
Malzeme sertliği [Shore A]	30.0 Shore A
Boyut	100.00
Körük Sayısı	1.5
Malzeme sertliği	60.0 Shore A
Bağlantı	G3/8-AG

SDC1 100 PU 30/60 G3/8-AG

Çeşitli çaplarda mevcut olan SDC1 vantuz, bağlantı nipeli monte edilmiş olarak tedarik edilir.



Tasarım verileri SDC1 100 PU 30/60 G3/8-AG

Tasarım verileri

Attribute	Value
Yükseklik H	51.00 mm
Dış çap D1	92.5 mm
Kafa çapı Dk	50.0 mm
Nominal çap dn	9.80 mm
d2	45.0 mm
Dış uzunluğu LG1	10.0 mm
Anahtar boyutu SW2	8.0 mm
Yay stroku Z	22.0 mm
Çap Ds	95.6 mm
Yükseklik H3	28.30 mm

Art.-Nr.: 10.01.06.05523

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Poliüretan PU
Malzeme sertliği [Shore A]	30.0 Shore A
Hortum çapı (tavsiye edilen) d	12.0 mm
İş parçası yarıçapı dak (dışbükey)	50.0 mm
Çekme kuvveti	276.70 N
Emme kuvveti (-600mbar)	95.40 N
Cilt	107.500 cm ³
Boyut	100.00
Sıcaklık direnci	55.0 °C
Körük Sayısı	1.5
Malzeme sertliği	60.0 Shore A
Bağlantı	G3/8-AG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.05523

**Yedek parçalar için sipariş verileri 10.01.06.05523**

Typ	Ürün numarası
Vantuz bağlantı nipel	SA-NIP N044 G3/8-AG DN800
	10.01.06.03372

