




SDC1 70 PU 30/60 G3/8-AG

Çeşitli çaplarda mevcut olan SDC1 vantuz, bağlantı nipeli monte edilmiş olarak tedarik edilir.



Tasarım verileri SDC1 70 PU 30/60 G3/8-AG

Teknik veriler

Attribute	Value
Vantuz malzemesi	Poliüretan PU
Malzeme sertliği [Shore A]	30.0 Shore A
Boyut	70.00
Körük Sayısı	1.5
Malzeme sertliği	60.0 Shore A
Bağlantı	G3/8-AG

Tasarım verileri

Attribute	Value
Yükseklik H	36.50 mm
Dış çap D1	74.0 mm
Kafa çapı Dk	50.0 mm
Nominal çap dn	9.80 mm
d2	24.0 mm
Dış uzunluğu LG1	10.0 mm
Anahtar boyutu SW2	8.0 mm
Yay stroku Z	18.0 mm
Çap Ds	70.0 mm
Yükseklik H3	18.50 mm

Art.-Nr.: 10.01.06.05530

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Poliüretan PU
Malzeme sertliği [Shore A]	30.0 Shore A
Hortum çapı (tavsiye edilen) d	12.0 mm
İş parçası yarıçapı dak (dışbükey)	30.0 mm
Çekme kuvveti	167.00 N
Emme kuvveti (-600mbar)	75.40 N
Cilt	52.000 cm ³
Boyut	70.00
Sıcaklık direnci	55.0 °C
Körük Sayısı	1.5
Malzeme sertliği	60.0 Shore A
Bağlantı	G3/8-AG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.05530

**Yedek parçalar için sipariş verileri 10.01.06.05530**

Typ	Ürün numarası
Vantuz bağlantı nipel	SA-NIP N044 G3/8-AG DN800
	10.01.06.03372

