




PSPF 33 SI-30/55 G3/8-IG

Körüklü vantuz PSPF (elastomer parça + bağlantı elemanı) monte edilmiş olarak teslim edilir. Ürün şunlardan oluşur:

- PSPF tipi vantuz - elastomer parça, çeşitli çaplarda mevcuttur
- SC tipi bağlantı elemanı - farklı dişlerle mevcuttur



Tasarım verileri PSPF 33 SI-30/55 G3/8-IG

Teknik veriler

Attribute	Value
Vantuz malzemesi	Silikon SI
Malzeme sertliği [Shore A]	30.0 Shore A
Boyut	33.00
Körük Sayısı	3.5
Malzeme sertliği	55.0 Shore A
Vakum bağlantısı	G3/8"-F

Tasarım verileri

Attribute	Value
Yükseklik H	57.50 mm
Nominal çap dn	11.00 mm
d2	14.0 mm
Diş G1	G3/8-IG
Diş uzunluğu LG1	12.0 mm
Anahtar boyutu SW1	22.0 mm
Yay stroku Z	14.5 mm
Çap Ds	33.0 mm
Çap Dmax(S)	33.5 mm

Art.-Nr.: 10.01.06.05592

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Silikon SI
Emme kuvveti (-600mbar)	24.00 N
Cilt	7.500 cm ³
Boyut	33.00
Körük Sayısı	3.5
Ürün ailesi	PSPF

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.05592

**Yedek parçalar için sipariş verileri 10.01.06.05592**

Typ	Ürün numarası
Körüklü vantuz (yuvarlak)	PSPF 33 SI-30/55 SC080 10.01.06.05502
Schmalz-Konnektör	SC 080 G3/8-IG 10.01.06.02594

WWW.SCHMALZ.COM/10.01.06.05592