


Art.-Nr.: 10.01.06.05600



PSPF 43 SI-30/55 G3/8-IG

Körüklü vantuz PSPF (elastomer parça + bağlantı elemanı) monte edilmiş olarak teslim edilir. Ürün şunlardan oluşur:

- PSPF tipi vantuz - elastomer parça, çeşitli çaplarda mevcuttur
- SC tipi bağlantı elemanı - farklı dişlerle mevcuttur



Tasarım verileri PSPF 43 SI-30/55 G3/8-IG

Teknik veriler

Attribute	Value
Vantuz malzemesi	Silikon SI
Malzeme sertliği [Shore A]	30,0 Shore A
Boyut	43,00
Körük Sayısı	3,5
Malzeme sertliği	55,0 Shore A
Vakum bağlantısı	G3/8"-F

Tasarım verileri

Attribute	Value
Yükseklik H	64,10 mm
Nominal çap dn	11,00 mm
d2	18,2 mm
Diş G1	G3/8-IG
Diş uzunluğu LG1	12,0 mm
Anahtar boyutu SW1	22,0 mm
Yay stroku Z	19,3 mm
Çap Ds	43,0 mm
Çap Dmax(S)	43,5 mm



Art.-Nr.: 10.01.06.05600

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Silikon SI
Emme kuvveti (-600mbar)	40,00 N
Cilt	16,651 cm ³
Boyut	43,00
Körük Sayısı	3,5
Ürün ailesi	PSPF

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.05600

**Sipariş Verisi Yedek Parça 10.01.06.05600**

Typ	Ürün numarası
Körüklü vantuz (yuvarlak)	PSPF 43 SI-30/55 SC080 10.01.06.05244
Schmalz-Konnektör	SC 080 G3/8-IG 10.01.06.02594

WWW.SCHMALZ.COM/10.01.06.05600