


Art.-Nr.: 10.01.06.05607



PSPF 53 SI-30/55 G3/8-AG

Körüklü vantuz PSPF (elastomer parça + bağlantı elemanı) monte edilmiş olarak teslim edilir. Ürün şunlardan oluşur:

- PSPF tipi vantuz - elastomer parça, çeşitli çaplarda mevcuttur
- SC tipi bağlantı elemanı - farklı dişlerle mevcuttur



Tasarım verileri PSPF 53 SI-30/55 G3/8-AG

Teknik veriler

Attribute	Value
Vantuz malzemesi	Silikon SI
Malzeme sertliği [Shore A]	30,0 Shore A
Boyut	53,00
Körük Sayısı	3,5
Malzeme sertliği	55,0 Shore A
Vakum bağlantısı	G3/8"-M

Tasarım verileri

Attribute	Value
Yükseklik H	63,50 mm
Nominal çap dn	10,30 mm
d2	22,4 mm
Diş G1	G3/8-AG
Diş uzunluğu LG1	10,0 mm
Anahtar boyutu SW1	27,0 mm
Yay stroku Z	25,3 mm
Çap Ds	53,0 mm
Çap Dmax(S)	54,5 mm



Art.-Nr.: 10.01.06.05607

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Silikon SI
Emme kuvveti (-600mbar)	61,00 N
Cilt	31,854 cm ³
Boyut	53,00
Körük Sayısı	3,5
Ürün ailesi	PSPF

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.05607

**Sipariş Verisi Yedek Parça 10.01.06.05607**

Typ	Ürün numarası
Körüklü vantuz (yuvarlak)	PSPF 53 SI-30/55 SC090
Schmalz-Konnektör	SC 090 G3/8-AG

WWW.SCHMALZ.COM/10.01.06.05607