




FSG 32 SI-MD-55 G1/4-IG

Teknik veriler

Attribute	Value
Vantuz malzemesi	Silikon SI metal algılanabilir
Malzeme sertliği [Shore A]	55.0 Shore A
Boyut	32.00
Körük Sayısı	2.5
Bağlantı	G1/4"-F
Meme ucu malzemesi	Alüminyum
Malzeme özellikleri	FDA uyumlu



Tasarım verileri FSG 32 SI-MD-55 G1/4-IG

Tasarım verileri

Attribute	Value
Yükseklik H	52.50 mm
Nominal çap dn	4.40 mm
d2	16.0 mm
Diş G1	G1/4"-F
Diş uzunluğu LG1	12.0 mm
Anahtar boyutu SW1	17.0 mm
Yay stroku Z	15.0 mm
Çap Ds	32.0 mm
Çap Dmax(S)	33.5 mm

Art.-Nr.: 10.01.06.05720

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Silikon SI metal algılanabilir
Malzeme sertliği [Shore A]	55.0 Shore A
Hortum çapı (tavsiye edilen) d	6.0 mm
İş parçası yarıçapı dak (dışbükey)	35.0 mm
Çekme kuvveti	36.90 N
Emme kuvveti (-600mbar)	12.06 N
Ağırlık	18.0 g
Cilt	10.000 cm ³
Boyut	32.00
Körük Sayısı	2.5
Ürün ailesi	FSG
Bağlantı	G1/4-IG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.05720

**Yedek parçalar için sipariş verileri 10.01.06.05720**

Typ	Ürün numarası
Körüklü vantuz (yuvarlak)	FG 32 SI-MD-55 N018
Vantuz bağlantı nipel	SA-NIP N018 G1/4-IG DN440

