




Teknik veriler

Attribute	Value
Vantuz malzemesi	Silikon SI metal algılanabilir
Malzeme sertliği [Shore A]	55.0 Shore A
Boyut	42.00
Körük Sayısı	2.5
Bağlantı	G1/4"-F
Meme ucu malzemesi	Alüminyum
Malzeme özellikleri	FDA uyumlu

FSG 42 SI-MD-55 G1/4-IG



Tasarım verileri

Attribute	Value
Yükseklik H	61.00 mm
Nominal çap dn	4.40 mm
d2	17.8 mm
Diş G1	G1/4"-F
Diş uzunluğu LG1	12.0 mm
Anahtar boyutu SW1	17.0 mm
Yay stroku Z	20.0 mm
Çap Ds	42.6 mm
Çap Dmax(S)	45.0 mm

Tasarım verileri FSG 42 SI-MD-55 G1/4-IG

Art.-Nr.: 10.01.06.05722

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Silikon SI metal algılanabilir
Malzeme sertliği [Shore A]	55.0 Shore A
Hortum çapı (tavsiye edilen) d	6.0 mm
İş parçası yarıçapı dak (dışbükey)	75.0 mm
Çekme kuvveti	44.00 N
Emme kuvveti (-600mbar)	14.93 N
Ağırlık	27.0 g
Cilt	19.786 cm ³
Boyut	42.00
Körük Sayısı	2.5
Ürün ailesi	FSG
Bağlantı	G1/4-IG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.05722

**Yedek parçalar için sipariş verileri 10.01.06.05722**

Typ	Ürün numarası
Körüklü vantuz (yuvarlak)	FG 42 SI-MD-55 N018
Vantuz bağlantı nipel	SA-NIP N018 G1/4-IG DN440

