


FGA 20 HT1-60 N016

Technical data

Attribute	Value
Suction cup material	High temperature material HT1
Material hardness [Shore A]	60.0 Shore A
Size	20.00
Number of folds	1.5
Applications	Sheet metal / metal



Design data FGA 20 HT1-60 N016

Design data

Attribute	Value
Height H2	3.80 mm
Height H	13.80 mm
Outside diameter D1	18.3 mm
Head diameter Dk	10.0 mm
d2	10.1 mm
Internal diameter d	4.80 mm
Spring stroke Z	5.0 mm
Diameter Ds	16.7 mm
Height H3	5.80 mm
Diameter Dmax(S)	20.0 mm



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.05777