

Art.-Nr.: 10.01.06.05781




SAOXB 60x30 ED-85 SC043

Technical data

Attribute	Value
Suction cup material	Elastodur ED
Material hardness [Shore A]	85.0 Shore A
Number of folds	1.5
Dimension (LxW)	60x30

Design data

Attribute	Value
Length L1	59.20 mm
Width B1	29.50 mm
Height H2	1.50 mm
Height H	25.00 mm
Head length Lk	41.00 mm
Spring stroke Z	10.5 mm
Suction cup width Bs	30.00 mm
Ls	60.00 mm
Lmax.(S)	63.00 mm
Bmax(S)	34.00 mm
Bk	23.00 mm
Length L2	45.60 mm
Width B2	15.60 mm



Design data SAOXB 60x30 ED-85 SC043

Bellows suction cup (oval)

SAOXB 60x30 ED-85 SC043



Art.-Nr.: 10.01.06.05781



Technical data

Attribute	Value
Suction cup material	Elastodur ED
Product family	SAOXB

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.05781



WWW.SCHMALZ.COM/10.01.06.05781