

Art.-Nr.: 10.01.06.05782




SAOXB 80x40 ED-85 SC043

Technical data

Attribute	Value
Suction cup material	Elastodur ED
Material hardness [Shore A]	85.0 Shore A
Number of folds	1.5
Dimension (LxW)	80x40

Design data

Attribute	Value
Length L1	78.80 mm
Width B1	39.00 mm
Height H2	1.50 mm
Height H	28.70 mm
Head length Lk	88.80 mm
Spring stroke Z	14.0 mm
Suction cup width Bs	39.00 mm
Ls	80.00 mm
Lmax.(S)	84.00 mm
Bmax(S)	46.00 mm
Bk	23.00 mm
Length L2	63.00 mm
Width B2	23.00 mm



Design data SAOXB 80x40 ED-85 SC043

Bellows suction cup (oval)

SAOXB 80x40 ED-85 SC043



Art.-Nr.: 10.01.06.05782



Technical data

Attribute	Value
Suction cup material	Elastodur ED
Product family	SAOXB

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.05782



WWW.SCHMALZ.COM/10.01.06.05782