




SAOXB 80x40 ED-85 SC043

Teknik veriler

Attribute	Value
Vantuz malzemesi	Elastodur ED
Malzeme sertliği [Shore A]	85,0 Shore A
Körük Sayısı	1,5
Boyutlar (LxW)	80x40

Tasarım verileri

Attribute	Value
Uzunluk L1	78,80 mm
Genişlik B1	39,00 mm
Yükseklik H2	1,50 mm
Yükseklik H	28,70 mm
Kafa uzunluğu Lk	88,80 mm
Yay stroku Z	14,0 mm
Vantuz genişliği Bs	39,00 mm
Ls	80,00 mm
Lmaks.(S)	84,00 mm
Bmaks(S)	46,00 mm
Bk	23,00 mm
Uzunluk L2	63,00 mm
Genişlik B2	23,00 mm



Tasarım verileri SAOXB 80x40 ED-85 SC043

Körüklü vantuz (oval)

SAOXB 80x40 ED-85 SC043



Art.-Nr.: 10.01.06.05782



Teknik veriler

Attribute	Value
Vantuz malzemesi	Elastodur ED
Ürün ailesi	SAOXB

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.05782



WWW.SCHMALZ.COM/10.01.06.05782