




SAOXB 110x55 ED-85 SC043

Teknik veriler

Attribute	Value
Vantuz malzemesi	Elastodur ED
Malzeme sertliği [Shore A]	85,0 Shore A
Körük Sayısı	1,5
Boyutlar (LxW)	110x55

Tasarım verileri

Attribute	Value
Uzunluk L1	108,50 mm
Genişlik B1	53,30 mm
Yükseklik H2	1,50 mm
Yükseklik H	34,40 mm
Kafa uzunluğu Lk	79,30 mm
Yay stroku Z	17,0 mm
Vantuz genişliği Bs	54,00 mm
Ls	110,00 mm
Lmaks.(S)	114,00 mm
Bmaks(S)	60,00 mm
Bk	34,00 mm
Uzunluk L2	89,00 mm
Genişlik B2	33,50 mm



Tasarım verileri SAOXB 110x55 ED-85 SC043

Körüklü vantuz (oval)

SAOXB 110x55 ED-85 SC043



Art.-Nr.: 10.01.06.05783



Teknik veriler

Attribute	Value
Vantuz malzemesi	Elastodur ED
Ürün ailesi	SAOXB

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.05783



WWW.SCHMALZ.COM/10.01.06.05783