




SAOXB 60x30 ED-85 RA MOD

Teknik veriler

Attribute	Value
Vantuz malzemesi	Elastodur ED
Malzeme sertliği [Shore A]	85,0 Shore A
Körük Sayısı	1,5
Boyutlar (LxW)	60x30
Meme ucu malzemesi	Alüminyum

Tasarım verileri

Attribute	Value
Uzunluk L1	59,20 mm
Genişlik B1	29,50 mm
Yükseklik H	32,50 mm
Nominal çap dn	4,50 mm
Yay stroku Z	10,5 mm
Uzunluk L4	31,80 mm
Vantuz genişliği Bs	30,00 mm
Ls	60,00 mm
Anahtar boyutu SW3	5,0 mm
Lmaks.(S)	63,00 mm
Bmax(S)	34,00 mm
Uzunluk L2	45,60 mm
Genişlik B2	15,60 mm



Tasarım verileri SAOXB 60x30 ED-85 RA MOD

Art.-Nr.: 10.01.06.06004

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Elastodur ED
Malzeme sertliği [Shore A]	85,0 Shore A
İş parçası yarıçapı dak (dışbükey)	15,0 mm
Çekme kuvveti	62,50 N
Emme kuvveti (-600mbar)	37,40 N
Yanal kuvvet	31,5 N
Yanal kuvvet yağlı yüzey	36,2 N
Cilt	13,700 cm ³
Körük Sayısı	1,5
Etkili emiş alanı	14,78 mm ²
Ürün ailesi	SAOXB
Boyutlar (LxW)	60x30
Meme ucu malzemesi	Alüminyum

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.06004

**Sipariş Verisi Yedek Parça 10.01.06.06004**

Typ	Ürün numarası
Körüklü vantuz (oval)	SAOXB 60x30 ED-85 SC043
	10.01.06.05781

