




SAOXB 80x40 ED-85 RA MOD

Teknik veriler

Attribute	Value
Vantuz malzemesi	Elastodur ED
Malzeme sertliği [Shore A]	85,0 Shore A
Körük Sayısı	1,5
Boyutlar (LxW)	80x40
Meme ucu malzemesi	Alüminyum

Tasarım verileri

Attribute	Value
Uzunluk L1	78,80 mm
Genişlik B1	39,00 mm
Yükseklik H	36,20 mm
Nominal çap dn	4,50 mm
Yay stroku Z	14,0 mm
Uzunluk L4	31,80 mm
Vantuz genişliği Bs	39,00 mm
Ls	80,00 mm
Anahtar boyutu SW3	5,0 mm
Lmaks.(S)	84,00 mm
Bmaks(S)	46,00 mm
Uzunluk L2	63,00 mm
Genişlik B2	23,00 mm



Tasarım verileri SAOXB 80x40 ED-85 RA MOD

SAOXB 80x40 ED-85 RA MOD

Art.-Nr.: 10.01.06.06018

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Elastodur ED
Malzeme sertliği [Shore A]	85,0 Shore A
İş parçası yarıçapı dak (dışbükey)	17,5 mm
Çekme kuvveti	96,60 N
Emme kuvveti (-600mbar)	76,10 N
Yanal kuvvet	42,8 N
Yanal kuvvet yağlı yüzey	50,4 N
Cilt	30,900 cm ³
Körük Sayısı	1,5
Etkili emiş alanı	26,52 mm ²
Ürün ailesi	SAOXB
Boyutlar (LxW)	80x40
Meme ucu malzemesi	Alüminyum

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.06018

**Sipariş Verisi Yedek Parça 10.01.06.06018**

Typ	Ürün numarası
Körüklü vantuz (oval)	SAOXB 80x40 ED-85 SC043
	10.01.06.05782

