




SAOXB 110x55 ED-85 RA MOD

Teknik veriler

Attribute	Value
Vantuz malzemesi	Elastodur ED
Malzeme sertliği [Shore A]	85,0 Shore A
Körük Sayısı	1,5
Boyutlar (LxW)	110x55
Meme ucu malzemesi	Alüminyum

Tasarım verileri

Attribute	Value
Uzunluk L1	108,50 mm
Genişlik B1	53,30 mm
Yükseklik H	42,00 mm
Nominal çap dn	4,50 mm
Yay stroku Z	17,0 mm
Uzunluk L4	31,80 mm
Vantuz genişliği Bs	54,00 mm
Ls	110,00 mm
Anahtar boyutu SW3	5,0 mm
Lmaks.(S)	114,00 mm
Bmax(S)	60,00 mm
Uzunluk L2	89,00 mm
Genişlik B2	33,50 mm



Tasarım verileri SAOXB 110x55 ED-85 RA MOD

SAOXB 110x55 ED-85 RA MOD

Art.-Nr.: 10.01.06.06033



Teknik veriler

Attribute	Value
Vantuz malzemesi	Elastodur ED
Malzeme sertliği [Shore A]	85,0 Shore A
İş parçası yarıçapı dak (dışbükey)	25,0 mm
Çekme kuvveti	190,10 N
Emme kuvveti (-600mbar)	155,00 N
Yanal kuvvet	91,7 N
Yanal kuvvet yağlı yüzey	97,6 N
Cilt	72,300 cm ³
Körük Sayısı	1,5
Etkili emiş alanı	49,73 mm ²
Ürün ailesi	SAOXB
Boyutlar (LxW)	110x55
Meme ucu malzemesi	Alüminyum

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.06033



Sipariş Verisi Yedek Parça 10.01.06.06033

Typ	Ürün numarası
Körüklü vantuz (oval)	SAOXB 110x55 ED-85 SC043
	10.01.06.05783

