


Art.-Nr.: 10.01.10.07012

**Technical data**


Attribute	Value
Shape mounting elements	Heavy duty 2 spring plunger
Utilization design	Mounting section
Spring stroke Z	25.0 mm
Size	40x40

FST-STARR 25 HD2 G1/2-AG G3/8-IG

The rigid suspension FST-STARR (retaining plate + spring plunger) is supplied as an individual part. To receive a complete rigid suspension (retaining plate + spring plunger + connection plate + accessories), the following ordering steps are required:

- Rigid suspension FST-STARR (step 1) – retaining plate + spring plunger, available with different strokes and number of spring plungers
- Connection plate FLAN-PL (step 2) – available for different area grippers

Available accessories: Flexolink (FLK), flange plate (FLAN-PL)

**Design data**

Attribute	Value
Length L	41.00 mm
Width B	152.00 mm
Height H1	129.00 mm
Height H2	20.00 mm
Height H	167.60 mm
Thread G1	G3/8"-F
Thread length LG1	13.0 mm
Thread G2	G1/2"-M
Thread length LG2	10.5 mm
Spring stroke Z	25.0 mm

Design data FST-STARR 25 HD2 G1/2-AG G3/8-IG



Suspension, rigid

FST-STARR 25 HD2 G1/2-AG G3/8-IG



Art.-Nr.: 10.01.10.07012



Technical data

Attribute	Value
Spring rate	3.828 N/mm
Weight	2,300.0 g
Product family	FST-STARR
Size	40x40



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.10.07012



Ordering Data Accessories 10.01.10.07012

Typ		Item number
Flange plate	FLAN-PL 120x85x10 ST FLGR	10.01.10.05701
Flange plate	FLAN-PL 160x120x10 FMHD	10.01.10.08805
Flange plate	FLAN-PL 200x100x10 ST SBX	10.01.11.02823
Flange plate	FLAN-PL 260x90x10 FLGR	10.01.10.05704
Flange plate	FLAN-PL 400x90x10 ST SBX	10.01.10.05702
Flexolink	FLK G1/2-IG G1/2-AG	10.01.03.00175
Flexolink	FLK G1/2-IG G1/2-AG V	10.01.03.00207



WWW.SCHMALZ.COM/10.01.10.07012