

Art.-Nr.: 10.01.12.01836




VC-M-SP 160x160x30

The Multi-Clamp suction plate is supplied in individual parts. The delivery consists of:

- Suction plate with mounted seal
- Manually operated valve
- Vacuum hose

Available spare parts: sealing profile, friction insert

Available accessories: accessory set for operating two suction plates with one pump or one ejector



Design data VC-M-SP 160x160x30

Technical data

Attribute	Value
Air consumption [l/min]	48.0 l/min
Air consumption	2.880 m ³ /h
Suction rate	2.300 m ³ /h
Length L	160.00 mm
Width B	160.00 mm
Height H	30.00 mm

Design data

Attribute	Value
Length L	160.00 mm
Width B	160.00 mm
Height H	30.00 mm
Internal diameter d	6.00 mm



Multi-Clamp - Suction plate
VC-M-SP 160x160x30



Art.-Nr.: 10.01.12.01836



Technical data

Attribute	Value
Weight	0.875 kg



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.12.01836



Ordering Data Accessories 10.01.12.01836

Typ		Artikelnummer
Sealing profile (meter)	DI-PROF 8x10.5 MOS EPDM-15	10.01.12.02056
Friction insert	REIB-INS 8.1x18 VC-M	10.01.12.02000
Multi-Base	VC-M-B 170x165x209	10.01.12.01854



Ordering Data Wear Parts 10.01.12.01836

Typ		Artikelnummer
Friction insert	REIB-INS 8.1x18 VC-M	10.01.12.02000
Sealing profile (meter)	DI-PROF 8x10.5 MOS EPDM-15	10.01.12.02056



WWW.SCHMALZ.COM/10.01.12.01836