



VC-M 165x165x220.5

Technical data


Attribute	Value
Air consumption [l/min]	48.0 l/min
Air consumption	2.880 m ³ /h
Suction rate	2.300 m ³ /h
Length L	165.00 mm
Width B	165.00 mm
Height H	220.50 mm

The Multi-Clamp system is delivered assembled. The product consists of:

- Suction plate with sealing
- Multi-Base with turning and swivelling unit
- Vacuum hose

Available spare parts: friction insert, sealing profile

Available accessories: Multi-Base VC-M-B, Multi-Clamp suction plate VC-M-SP, Multi-Base VC-M-BV, Multi-Clamp suction plate VC-M-SPV, Multi-Clamp vacuum pump VC-M-PU, foot-operated interrupter FU, accessories



Design data VC-M 165x165x220.5

Design data

Attribute	Value
Length L	165.00 mm
Width B	165.00 mm
Height H	220.50 mm

Art.-Nr.: 10.01.12.01845

**Technical data**

Attribute	Value
Weight	5.762 kg

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.12.01845**Ordering Data Accessories 10.01.12.01845**

Typ		Artikelnummer
Sealing profile (meter)	DI-PROF 8x10.5 MOS EPDM-15	10.01.12.02056
Friction insert	REIB-INS 8.1x18 VC-M	10.01.12.02000
Multi-Clamp - Suction plate	VC-M-SP 160x160x30	10.01.12.01836
Multi-Clamp - Suction plate	VC-M-SP 200x55	10.01.12.02003
Multi-Clamp - Suction plate	VC-M-SP 210	10.01.12.02002
Multi-Clamp - Suction plate	VC-M-SP 300x100	10.01.12.02052

