

Art.-Nr.: 10.01.12.01853

**Technical data**

Attribute	Value
Suction rate	3.000 m ³ /h
Length L	160.00 mm
Width B	160.00 mm
Height H	30.00 mm

VC-M-SPV 160x160x30

The Multi-Clamp suction plate is supplied in individual parts. The delivery consists of:


- Suction plate with mounted seal
- Manually operated valve
- Vacuum hose

Available spare parts: sealing profile, friction insert

Available accessories: accessory set for operating two suction plates with one pump or one ejector

Design data

Attribute	Value
Length L	160.00 mm
Width B	160.00 mm
Height H	30.00 mm
Internal diameter d	6.00 mm



Design data VC-M-SPV 160x160x30



Multi-Clamp - Suction plate

VC-M-SPV 160x160x30



Art.-Nr.: 10.01.12.01853



Technical data

Attribute	Value
Weight	0.896 kg



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.12.01853



Ordering Data Accessories 10.01.12.01853

Typ		Artikelnummer
Sealing profile (meter)	DI-PROF 8x10.5 MOS EPDM-15	10.01.12.02056
Foot-operated interrupter	FU 5 3/2 -	10.01.12.02055
Friction insert	REIB-INS 8.1x18 VC-M	10.01.12.02000
Multi-Base	VC-M-BV 265x170x209	10.01.12.02050
Multi-Clamp Vacuum pump	VC-M-PU 4 110V-AC	10.01.12.02051
Multi-Clamp Vacuum pump	VC-M-PU 4 230V-AC	10.01.12.02040
Accessories	ZUB VC-M-V	10.01.12.02054



Ordering Data Wear Parts 10.01.12.01853

Typ		Artikelnummer
Friction insert	REIB-INS 8.1x18 VC-M	10.01.12.02000
Sealing profile (meter)	DI-PROF 8x10.5 MOS EPDM-15	10.01.12.02056



WWW.SCHMALZ.COM/10.01.12.01853