

Art.-Nr.: 10.01.12.02050

**Technical data**

Attribute	Value
Length L	265.00 mm
Width B	170.00 mm
Height H	209.00 mm

VC-M-BV 265x170x209

The Multi-Clamp system is delivered assembled. The product consists of:

- Suction plate with sealing
- Multi-Base with turning and swivelling unit
- Vacuum hose

Available spare parts: friction insert, sealing profile

Available accessories: Multi-Base VC-M-B, Multi-Clamp suction plate VC-M-SP, Multi-Base VC-M-BV, Multi-Clamp suction plate VC-M-SPV, Multi-Clamp vacuum pump VC-M-PU, foot-operated interrupter FU, accessories

Design data

Attribute	Value
Length L	265.00 mm
Width B	170.00 mm
Height H	209.00 mm

Design data VC-M-BV 265x170x209

**Technical data**

Attribute	Value
Weight	7.340 kg



Art.-Nr.: 10.01.12.02050

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.12.02050**Ordering Data Accessories 10.01.12.02050**

Typ		Artikelnummer
Sealing profile (meter)	DI-PROF 8x10.5 MOS EPDM-15	10.01.12.02056
Foot-operated interrupter	FU 5 3/2 -	10.01.12.02055
Friction insert	REIB-INS 8.1x18 VC-M	10.01.12.02000
Multi-Clamp Vacuum pump	VC-M-PU 4 110V-AC	10.01.12.02051
Multi-Clamp Vacuum pump	VC-M-PU 4 230V-AC	10.01.12.02040
Multi-Clamp - Suction plate	VC-M-SPV 160x160x30	10.01.12.01853
Multi-Clamp - Suction plate	VC-M-SPV 200x55	10.01.12.02009
Multi-Clamp - Suction plate	VC-M-SPV 210	10.01.12.02008
Multi-Clamp - Suction plate	VC-M-SPV 300x100	10.01.12.02053
Accessories	ZUB VC-M-V	10.01.12.02054

