

Art.-Nr.: 10.01.12.04574

**Technical data**

Attribute	Value
Height H	100.00 mm
Arrangement	Can be turned 360°
Version	PRO
Dimension (LxW)	125x75
Dimension suction plate bottom	160x115 mm


VCBL-K2-PRO 125x75x100 D-360

The vacuum block VCBL-K2-PRO is delivered assembled. The product consists of:

- Top suction plate of type VCSP-O - elastomer part, available in various dimensions and suction areas
- Base body made of plastic
- Bottom suction plate type VCSP-U - Elastomer part

Available spare parts: suction plate (top), wear parts set, suction plate (bottom), sealing frame, friction plate, spare parts set with steel inserts, touch valve

Available accessories: Suction plate foam rubber

**Design data**

Attribute	Value
Length L1	160.00 mm
Length L	125.00 mm
Width B	75.00 mm
Height H2	73.00 mm
Height H	100.00 mm

Design data VCBL-K2-PRO 125x75x100 D-360



Art.-Nr.: 10.01.12.04574

**Technical data**

Attribute	Value
Dimension suction plate bottom	160x115 mm

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.12.04574**Ordering Data Accessories 10.01.12.04574**

Typ	Item number
Suction plate (top)	VCSP-O 125x75x17.7 MOS TPE 10.01.12.03511

**Ordering Data Spare Parts 10.01.12.04574**

Typ	Item number
Suction plate (top)	VCSP-O 125x75x15.5 TPE 10.01.12.00011
Suction plate (bottom)	VCSP-U 160x115x16.5 VCBL-K2 TPE 10.01.12.04402
Set of parts subject to wear	VST VCBL-K2 10.01.12.02149
Vacuum block guide strip	VCFL 152x126x26.5 VCBL-K2 10.01.12.04059

