

Art.-Nr.: 10.01.12.04584

**Technical data**

Attribute	Value
Height H	100.00 mm
Arrangement	Can be turned 360°
Version	PRO
Dimension (LxW)	120x50
Dimension suction plate bottom	160x115 mm


VCBL-K2-PRO 120x50x100 D-360

The vacuum block VCBL-K2-PRO is delivered assembled. The product consists of:

- Top suction plate of type VCSP-O - elastomer part, available in various dimensions and suction areas
- Base body made of plastic
- Bottom suction plate type VCSP-U - Elastomer part

Available spare parts: suction plate (top), wear parts set, suction plate (bottom), sealing frame, friction plate, spare parts set with steel inserts, touch valve

Available accessories: Suction plate foam rubber

**Design data**

Attribute	Value
Length L1	160.00 mm
Length L	120.00 mm
Width B	50.00 mm
Height H2	73.00 mm
Height H	100.00 mm

Design data VCBL-K2-PRO 120x50x100 D-360



Art.-Nr.: 10.01.12.04584

**Technical data**

Attribute	Value
Dimension suction plate bottom	160x115 mm

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.12.04584

**Ordering Data Accessories 10.01.12.04584**

Typ		Item number
Suction plate (top)	VCSP-O 120x50x15.5 TPE	10.01.12.00012
Suction plate (bottom)	VCSP-U 160x115x16.5 VCBL-K2 TPE	10.01.12.04402
Vacuum block guide strip	VCFL 152x126x26.5 VCBL-K2	10.01.12.04059
Set of parts subject to wear	VST VCBL-K2	10.01.12.02149

