

Art.-Nr.: 10.01.12.04746

**Technical data**

Attribute	Value
Height H	85.00 mm
Additional function vacuum block	Toolless height adjustment
Stroke Z	9.00 mm
Dimension (LxW)	170x135
Clamping range [mm]	15.0 ... 85.0 mm
Shape	QUICK


VCMC-K1-QUICK 170x135x85 15-85

The mechanical clamp VCMC-K1-QUICK is delivered completely assembled. The product consists of:

- Clamping disc with quick adjustment
- Main body made of aluminum
- Mount on the console with mechanical clamping

Available spare parts: clamping disc, sealing frame, clamping unit

Available accessories: clamping range extension, clamping unit

**Design data**

Attribute	Value
Length L	171.00 mm
Width B	133.30 mm
Height H1	202.50 mm
Height H2	30.00 mm
Height H	85.00 mm
Outside diameter D1	56.0 mm
Hole spacing X1	66.5 mm
Hole spacing X2	44.0 mm

Design data VCMC-K1-QUICK 170x135x85 15-85



Art.-Nr.: 10.01.12.04746

**Technical data**

Attribute	Value
Clamping range [mm]	15.0 ... 85.0 mm

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.12.04746**Ordering Data Accessories 10.01.12.04746**

Typ		Artikelnummer
Extension with hexagon	VRL-S M20x1x35	10.01.12.04374
Accessories-clamping systems	ZUB VCMC	10.01.12.04008
Clamping unit	KLEM-EINH 69.5x35x12.5	10.01.12.04990

**Ordering Data Spare Parts 10.01.12.04746**

Typ		Artikelnummer
Clamping unit	KLEM-EINH 69.5x28.5x12.5 VCMC-K1	10.01.12.04835
Clamping disc	SPAN-TELL 110x30 EXZ VCMC	10.01.12.04688
Sealing frame (bottom)	VCDR 166x113x6.6 VCBL-K1	10.01.12.03629

