

Art.-Nr.: 10.01.12.05327

**Technical data**

Attribute	Value
Height H	125.00 mm
Arrangement	insertable 360°/15°
Additional function vacuum block	Touch valve
Dimension (LxW)	170x128
Shape	Heavy duty


VCBL-K2-HD 170x128x125 S-360-15 TV

The vacuum block VCBL-K2-HD is delivered assembled. The product consists of:

- Expandable and replaceable suction plate with sealing cord, available in different dimensions
- Base body made of aluminum, optionally with mechanical clamp

Available spare parts: Sealing cord, suction plate

Available accessories: Clamping

Design data

Attribute	Value
Length L1	170.00 mm
Length L	170.00 mm
Width B1	128.00 mm
Width B	128.00 mm
Height H1	132.00 mm
Height H	125.00 mm

Design data VCBL-K2-HD 170x128x125 S-360-15 TV

Art.-Nr.: 10.01.12.05327

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.12.05327**Ordering Data Accessories 10.01.12.05327**

Typ		Artikelnummer
Clamping unit	KLEM-EINH 70x24.5x4.5 VCMC-K2	10.01.12.04255

**Ordering Data Spare Parts 10.01.12.05327**

Typ		Artikelnummer
Suction plate (top)	VCSP-O 170x128x19.5 RB AL	10.01.12.05226
Sealing frame (bottom)	VCDR 166x113x6.6 VCSP	10.01.12.02191
O-ring	O-RING 50x2.5 NBR-70	10.07.08.00073
Touch Valve	TV D9 4.3	10.01.12.02514
Machine screw	SCHR 4762 M10x30 ST-8.8 VZ	20.01.02.02003
Sealing profile (meter)	DI-PROF 4x6 MOS NK-20 HR	10.07.04.00054

