


Art.-Nr.: 10.01.14.00231

**Technical data**

Attribute	Value
Length L	195.00 mm
Width B	195.00 mm
Height H	11.00 mm


ISAP-S4 195x195x11

The Adapter-Plates ISAP-S4 are delivered assembled. The products consist of:

- main body of aluminum
- sealing magnets for closing the vacuum openings

Available spare parts: sealing magnet, wear part set

Available accessories: Mono-Base, spacer ring, suction cup

**Design data**

Attribute	Value
Length L1	145.00 mm
Length L	195.00 mm
Width B1	145.00 mm
Width B	195.00 mm
Height H1	28.00 mm
Height H	11.00 mm

Design data ISAP-S4 195x195x11



Art.-Nr.: 10.01.14.00231

**Technical data**

Attribute	Value
Weight	0.360 kg

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.14.00231**Ordering Data Accessories 10.01.14.00231**

Typ		Artikelnummer
Cup	ISCUP Cup 1 80x80x16	10.01.15.00209
Cup	ISCUP Cup 2 80x40x16	10.01.15.00210
Cup	ISCUP Cup 3 80x28x16	10.01.15.00211
Mono-Base	ISMB 80x80x8	10.01.15.00188
Spacer ring, Innospann	ISZR-V 80x15	10.01.15.00052

**Ordering Data Spare Parts 10.01.14.00231**

Typ		Artikelnummer
Sealing magnet	ISMST 19-7 4ISMST	10.01.14.00847
Spacer ring, Innospann	ISZR-V 80x15	10.01.15.00052

**Ordering Data Wear Parts 10.01.14.00231**

Typ		Artikelnummer
Sealing frame (bottom)	VCDR 141x77.2x5.1 VCBL-S	10.01.12.03138
Set of parts subject to wear	VST VCBL-S DI-RA	10.01.12.03318

