

Technical data

Attribute	Value
Dimension (LxW)	175x175
Recommended slot width x slot depth [mm]	5/7
Length L	175.00 mm
Width B	175.00 mm
Height H	7.00 mm
Grid	30/50


ISAP-R 175x175x7 30/50

The adapter plate ISAP-R is delivered assembled. The product consists of:

- Base plate made of steel
- Sealing magnets for closing the vacuum openings

Available spare parts: sealing magnet

Available accessories: Mono-Base, suction cup



Design data

Attribute	Value
Length L	175.00 mm
Width B	175.00 mm
Height H	7.00 mm

Design data ISAP-R 175x175x7 30/50

Art.-Nr.: 10.01.15.00184

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.15.00184**Ordering Data Accessories 10.01.15.00184**

Typ		Artikelnummer
Cup	ISCUP Cup 1 80x80x30	10.01.15.00003
Cup	ISCUP Cup 2 80x40x30	10.01.15.00004
Cup	ISCUP Cup 3 80x28x30	10.01.15.00005
Mono-Base	ISMB 80x80x8	10.01.15.00188
Sealing magnet	ISMST 19-7 4ISMST	10.01.14.00847

**Ordering Data Spare Parts 10.01.15.00184**

Typ		Artikelnummer
Sealing magnet	ISMST 19-7 4ISMST	10.01.14.00847

**Ordering Data Wear Parts 10.01.15.00184**

Typ		Artikelnummer
Sealing frame	ISDR 167x167x9.3 NBR-55	10.01.15.00182