


Art.-Nr.: 10.01.15.00296

**Technical data**

Attribute	Value
Recommended slot width x slot depth [mm]	5/7
Length L	160.00 mm
Width B	160.00 mm
Height H	16.00 mm
Grid	50x50
for	Grid table systems
Working height H (AH)	45.00 mm


AP-R-160x160x16-50x50

The adapter plate AP-R is delivered assembled. The product consists of:

- Main body made of aluminum
- Bottom sealing frame

Available spare parts: sealing frame

Available accessories: vacuum blocks

**Design data**

Attribute	Value
Length L	160.00 mm
Width B	160.00 mm
Height H	16.00 mm

Design data AP-R-160x160x16-50x50



Art.-Nr.: 10.01.15.00296

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.15.00296**Ordering Data Accessories 10.01.15.00296**

Typ		Artikelnummer
Vacuum block	VCBL-B 140x130x29 TV	10.01.12.03165
Vacuum block	VCBL-B 125x75x29 TV	10.01.12.03166
Vacuum block	VCBL-B 120x50x29 TV	10.01.12.03167
Vacuum block	VCBL-B 130x30x29 TV	10.01.12.03168
Vacuum block	VCBL-B 140x130x48 TV	10.01.12.03169
Vacuum block	VCBL-B 125x75x48 TV	10.01.12.03170
Vacuum block	VCBL-B 120x50x48 TV	10.01.12.03171
Vacuum block	VCBL-B 130x30x48 TV	10.01.12.03172
Vacuum block	VCBL-B 140x130x74 TV	10.01.12.03173
Vacuum block	VCBL-B 125x75x74 TV	10.01.12.03174
Vacuum block	VCBL-B 120x50x74 TV	10.01.12.03175
Vacuum block	VCBL-B 130x30x74 TV	10.01.12.03176

**Ordering Data Wear Parts 10.01.15.00296**

Typ		Artikelnummer
Sealing frame	ISDR 150x150x13.5 R 30/50	10.01.15.00352

