

Art.-Nr.: 10.01.15.00564

**Technical data**


Attribute	Value
Utilization design	Steel-Plate
Length L	135.00 mm
Width B	135.00 mm
Height H	156.00 mm
Slewing angle W	15.0 °
Stroke Z	29.50 mm

UB 135x135x156 29.5 15 ISST

The Basic Holding Fixture BHF clamping system from Schmalz is not supplied assembled. The system consists of several components which are ordered independently of each other:

- Uni-Base UB suitable for Schmalz Steel-Plate ISST-MPL or for a flat table
- Innospann Vacuum Cups ISCUP
- Schmalz Balance SSPB suction plate with matching Innospann mounting

Available accessories: Reference suction cup

**Design data**

Attribute	Value
Length L	135.00 mm
Width B	135.00 mm
Height H	156.00 mm
Outside diameter D1	6.0 mm
Outside diameter D2	8.0 mm
Outside diameter D	60.50 mm
Slewing angle W	15.0 °
Stroke Z	29.50 mm

Design data UB 135x135x156 29.5 15 ISST



Art.-Nr.: 10.01.15.00564

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.15.00564**Discontinued item**

The product family will be discontinued and is available until **01.01.2026**
Starting from this time, the article can no longer be ordered.
alternative article

**Ordering Data Accessories 10.01.15.00564**

Typ		Artikelnummer
Suction Cup Balance SSCB	SSCB-78 93.5-107.5 ZP 60 SAB-NBR	10.01.15.00572
Cup	ISCUP Cup 1 80x80x30	10.01.15.00003
Cup	ISCUP Cup 2 80x40x30	10.01.15.00004
Cup	ISCUP Cup 3 80x28x30	10.01.15.00005
Schmalz Suction Plate Balance	SSPB-117 117-125 NBR	10.01.15.00719
Referenz Suction-Cup	RSC 85x120-VU1-40-IS-BHF	10.01.15.00587