

Art.-Nr.: 10.01.15.00572

**Technical data**


Attribute	Value
Material hardness [Shore A]	60.0 Shore A
Connection	Ø60mm
Height H1	117.30 mm
Dmk	78.0 mm
Suction cup type	Bellows suction cups SAB
Function suction cup	Centrally fixed pins
Material	NBR
Material workpiece support	NBR
Working area [mm]	93.5 ... 107.5

SSCB-78 93.5-107.5 ZP 60 SAB-NBR

The Suction Cup Balance SSCB is delivered assembled. The delivery consists of:

- Suction Cup Balance made of aluminium; with positioning pins
- Suction cups FSG-VU1 or SAB-NBR

Available spare parts: Suction cups (spare parts set), cover cap

Design data

Attribute	Value
Height H1	117.30 mm
Outside diameter D1	116.4 mm
Outside diameter D	60.00 mm
Dmk	78.0 mm
Stroke Z	22.00 mm
Operating height EH (min.)	93.50 mm
Operating height EH (max.)	107.50 mm
Suction stroke Zs	14.0 mm

Design data SSCB-78 93.5-107.5 ZP 60 SAB-NBR



SSCB-78 93.5-107.5 ZP 60 SAB-NBR

Art.-Nr.: 10.01.15.00572

**Technical data**

Attribute	Value
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	60.0 Shore A
Weight	1,300.0 g
Size	60.00

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.15.00572**Ordering Data Spare Parts 10.01.15.00572**

Typ		Artikelnummer
Bellows suction cups (round)	SABT-C 60 NBR-60 M10-AG	10.01.06.01878
Cap (round)	KAPP 7x10.5 SSCB	10.01.15.00918

