

Art.-Nr.: 10.01.15.00922

**Technical data**


Attribute	Value
Material hardness [Shore A]	72.0 Shore A
Connection	M6-F
Height H1	179.00 mm
Dmk	78.0 mm
Suction cup type	Bellows suction cups FSG
Function suction cup	Centrally fixed pins
Material	VU1
Material workpiece support	NBR
Working area [mm]	141.0 ... 171.0

SSCB-78 141-171 ZP M6-IG FSG-VU1

The Suction Cup Balance SSCB is delivered assembled. The delivery consists of:

- Suction Cup Balance made of aluminium; with positioning pins
- Suction cups FSG-VU1 or SAB-NBR

Available spare parts: Suction cups (spare parts set), cover cap

**Design data**

Attribute	Value
Height H1	179.00 mm
Outside diameter D1	134.0 mm
Thread G1	M6-F
Thread G2	G1/4"-F
Dmk	78.0 mm
Pitch diameter D mk1	48.0 mm
Stroke Z	46.00 mm
Operating height EH (min.)	141.00 mm
Operating height EH (max.)	171.00 mm
Suction stroke Zs	30.0 mm

Design data SSCB-78 141-171 ZP M6-IG FSG-VU1



SSCB-78 141-171 ZP M6-IG FSG-VU1

Art.-Nr.: 10.01.15.00922



Technical data

Attribute	Value
Suction cup material	Vulkollan VU1
Material hardness [Shore A]	72.0 Shore A
Weight	2,609.7 g
Size	60.00



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.15.00922



Ordering Data Accessories 10.01.15.00922

Typ	Artikelnummer
Set of spare parts	ERS SSCB-FG60-VU1 10.01.15.00953



Ordering Data Spare Parts 10.01.15.00922

Typ	Artikelnummer
Set of spare parts	ERS SSCB-FG60-VU1 10.01.15.00953
Cap (round)	KAPP 7x10.5 SSCB 10.01.15.00918

